









# ProSim family comparison guide

## Functions

ProSim family								
	ProSim 8 + SPOT	ProSim 8	ProSim 4 + SPOT Light	ProSim 4	ProSim 3	ProSim 2	SPOT Light	PS410
<b>ECG simulation</b>	•	•	•	•	•	•		•
<b>Arrhythmia waveform selection</b>	50+	50+	11	43	43	43		
<b>Respiration simulation</b>	•	•	•	•	•	•		
<b>IBP simulation (channels)</b>	2	2	1	1	4	2		
<b>Temperature</b>	•	•			•	•		
<b>NIBP simulation</b>	•	•	•	•				
<b>Manometer (pressure meter)</b>	•	•	•	•				
<b>Leak test</b>	•	•	•	•				
<b>Pressure relief test</b>	•	•	•	•				
<b>Fetal ECG/IUP simulation</b>	•	•			•			
<b>Cardiac output</b>	•	•			•			
<b>Rainbow SET (masimo) test</b>	•							
<b>Optical SpO<sub>2</sub></b>	•		•				•	

## Features

	ProSim 8 + SPOT	ProSim 8	ProSim 4 + SPOT Light	ProSim 4	ProSim 3	ProSim 2	SPOT Light	PS410
<b>Multi-parameter simulation</b>	•	•	•	•	•	•		
<b>Presets, Auto sequences</b>	•	•	•	•				•
<b>Multi-language</b>	•	•	•	•			•	
<b>PC control software (Ansur)</b>	•	•						
<b>Direct data saving and printing</b>	•	•						
<b>Barcode scanning</b>	•	•						
<b>Wireless control</b>	•	•						
<b>Remote operation</b>	•	•			•	•		
<b>Communication</b>	USB, USB, wireless	USB, USB, wireless	USB	USB	USB	USB	USB	
<b>Display</b>	LCD color	LCD color	Touchscreen	Touchscreen	LCD gray	LCD gray	LCD gray	LCD
<b>Battery life</b>	9 hours	9 hours	4 hours	4 hours	8 hours	8 hours	10 hours	8 hours

